

Varistar CP Cabinet Frame, Seismic

Power Utilities

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

VLASTNOSTI

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Výška	Šířka	Hloubka	Shock and Vibration Tolerance	Barva
20630-358	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-359	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-360	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-361	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-362	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-363	38 U	1800 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-364	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey

Katalogové číslo	Rack Height	Výška	Šířka	Hloubka	Shock and Vibration Tolerance	Barva
20630-365	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-366	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-367	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-368	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-369	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-370	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-371	42 U	2000 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-372	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-373	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-374	47 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-375	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-376	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-377	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Katalogové číslo	Kód barvy	Complies With	Frame Material	Materiál	Product Type	Static Load
20630-358	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-359	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-360	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf

Katalogové číslo	Kód barvy	Complies With	Frame Material	Materiál	Product Type	Static Load
20630-361	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-362	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-363	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel		Cabinet/Rack Frame	1600 kgf
20630-364	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-365	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-366	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-367	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-368	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-369	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-370	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-371	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-372	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-373	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-374	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-375	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-376	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf
20630-377	RAL 7021	IEC 61587-1, IEC 61587-2	Ocel	Ocel	Cabinet/Rack Frame	1600 kgf

Table 3/3

Katalogové číslo	Typ	Works With
------------------	-----	------------

20630-358	Seismic	Varistar CP
20630-359	Seismic	Varistar CP
20630-360	Seismic	Varistar CP
20630-361	Seismic	Varistar CP
20630-362	Seismic	Varistar CP
20630-363	Seismic	Varistar CP
20630-364	Seismic	Varistar CP
20630-365	Seismic	Varistar CP
20630-366	Seismic	Varistar CP
20630-367	Seismic	Varistar CP
20630-368	Seismic	Varistar CP
20630-369	Seismic	Varistar CP
20630-370	Seismic	Varistar CP
20630-371	Seismic	Varistar CP
20630-372	Seismic	Varistar CP
20630-373	Seismic	Varistar CP
20630-374	Seismic	Varistar CP
20630-375	Seismic	Varistar CP
20630-376	Seismic	Varistar CP

20630-377	Seismic	Varistar CP
-----------	---------	-------------

DALŠÍ PODROBNOSTI O PRODUKTU

Please order attachments and components separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE