

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Power Utilities

Non-shielded subrack for backplane mounting.



CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Rukojeť v ceně
24563-131	3 U	175 mm	1	Backplane	160 mm	No
24563-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	No
24563-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No
24563-135	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No
24563-136	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No
24563-431	6 U	175 mm	1	Backplane	160 mm	No
24563-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	No
24563-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24563-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No
24563-435	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No
24563-436	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	No

Table 2/2

Katalogové číslo	Mounting	Complies With	EMC Shielding	Product Type	Rack Width	Static Load
24563-131	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-132	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf

Katalogové číslo	Mounting	Complies With	EMC Shielding	Product Type	Rack Width	Static Load
24563-133	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-134	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-135	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-136	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-431	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-432	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-433	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-434	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-435	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf
24563-436	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP	11 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE