

Front Panel, Unshielded, With Fastener Pin

Power Utilities



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICATIONS



VLASTNOSTI

Enable grounding of the front area (protection class 1)

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish	Treated Edges
20119-161	21 HP	1	Screw-on Front	Anodized	Conductive	No
20119-163	42 HP	1	Screw-on Front	Anodized	Anodized	No
20119-162	28 HP	1	Screw-on Front	Anodized	Conductive	No
20119-160	14 HP	1	Screw-on Front	Anodized	Conductive	No

Katalogové číslo	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/3

Katalogové číslo	Complies With	EMC Shielding	Výška	Materiál	Product Type	Rack Height
20119-161	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Hliník	Front Panel	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Hliník	Front Panel	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Hliník	Front Panel	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Hliník	Front Panel	3 U
20119-159	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Hliník	Front Panel	3 U

Table 3/3

Katalogové číslo	Typ	Šířka
20119-161	Front Panel without Handle	106.3 mm
20119-163	Front Panel without Handle	213 mm
20119-162	Front Panel without Handle	141.9 mm
20119-160	Front Panel without Handle	70.8 mm
20119-159	Front Panel without Handle	35.2 mm

DALŠÍ PODROBNOSTI O PRODUKTU

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE