


Guide Rail Accessories for Heavy PCBs, Extra Strong

Power Utilities



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICATIONS



VLASTNOSTI

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

SPECIFIKACE

Table 1/2

Katalogové číslo	Board Depth	Groove Width	Barva	Materiál	Produktová řada	Product Type
------------------	-------------	--------------	-------	----------	-----------------	--------------

34562-885	400 mm	2	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-883	280 mm	2	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-882	220 mm	2	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-884	340 mm	2	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-881	160 mm	2	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-883	280 mm	2.5	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

34564-885	400 mm	2.5	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-882	220 mm	2.5	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-881	160 mm	2.5	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-884	340 mm	2.5	Silver	Hliník	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

Table 2/2

Katalogové číslo	Typ	Works With
34562-885	Heavy Duty	Subracks, Cases, Chassis
34562-883	Heavy Duty	Subracks, Cases, Chassis
34562-882	Heavy Duty	Subracks, Cases, Chassis
34562-884	Heavy Duty	Subracks, Cases, Chassis
34562-881	Heavy Duty	Subracks, Cases, Chassis

Katalogové číslo	Typ	Works With
34564-883	Heavy Duty	Subracks, Cases, Chassis
34564-885	Heavy Duty	Subracks, Cases, Chassis
34564-882	Heavy Duty	Subracks, Cases, Chassis
34564-881	Heavy Duty	Subracks, Cases, Chassis
34564-884	Heavy Duty	Subracks, Cases, Chassis

DALŠÍ PODROBNOSTI O PRODUKTU

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE