

# Interscale for Embedded NUC, Conduction Cooled, 44 x 112 x 107 mm

## KATALOGOVÉ ČÍSLO

**14830-002**



Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

## CERTIFICATIONS



## VLASTNOSTI

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Compliant with the SDT.03 embeddedNUC standard <http://www.sget.org/standards.html>

Cutouts specific for IES MB95 embedded NUC board (<http://en.ies.de/>)

Integrated EMC protection

Integrated heat sink on top cover with 5 mm heat fins

Rigid construction requires only two screws

Color RAL 7016

Board mounting studs installed

Other dimensions, cutout shapes or locations, and screen printing available

## VLASTNOSTI PRODUKTU

Product Type: Small Form Factor Case

Produktová řada: Interscale

Typ: Desktop

Výška: 43.7mm

Šířka: 112mm

Hloubka: 106.5mm

Materiál: Hliník

Barva: Anthracite Grey

Kód barvy: RAL 7016

Povrchová úprava: Strukturovaný Práškový

Stupeň krytí: IP20

Cooling: Conduction Cooled

Množství v balení: 1

Net Weight: 0.3kg

## DALŠÍ PODROBNOSTI O PRODUKTU

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE