


Backplane With Through-Connected Signal Lines

Backplane with Through Connected Signal Lines.



CERTIFICATIONS



VLASTNOSTI

Power supply at each connector position (row 1 + 32)

Adaptation fields for power connections on 2-layer backplanes

SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-188	Backplane	28	3U	60 Signal Lines	3HP	
23007-010	Backplane	10	3U	60 Signal Lines	4HP	C64F
23007-081	Backplane	21	3U	60 Signal Lines	4HP	
23007-114	Backplane	14	3U	60 Signal Lines	3HP	C64F

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-040	Backplane	10	3U	60 Signal Lines	4HP	C96F
23007-410	Backplane	10	3U	90 Signal Lines	4HP	C96F
23007-021	Backplane	21	3U	60 Signal Lines	4HP	C64F
23007-421	Backplane	21	3U	90 Signal Lines	4HP	C96F
23007-051	Backplane	21	3U	60 Signal Lines	4HP	C96F
23007-128	Backplane	28	3U	60 Signal Lines	3HP	C64F
23007-158	Backplane	28	3U	60 Signal Lines	3HP	C96F

Table 2/2

Katalogové číslo	Power Connector Type	Množství v balení	Rychlé odeslání
23007-188	Fastons 6.3 x 0.8 mm	1	Ne
23007-010	Fastons 6.3 x 0.8 mm	1	Ne
23007-081	Fastons 6.3 x 0.8 mm	1	Ne
23007-114	Fastons 6.3 x 0.8 mm	1	Ne
23007-040	Fastons 6.3 x 0.8 mm	1	Ne
23007-410	Fastons 6.3 x 0.8 mm	1	Ne
23007-021	Fastons 6.3 x 0.8 mm	1	Ne
23007-421	Fastons 6.3 x 0.8 mm	1	Ne
23007-051	Fastons 6.3 x 0.8 mm	1	Ne
23007-128	Fastons 6.3 x 0.8 mm	1	Ne

Katalogové číslo	Power Connector Type	Množství v balení	Rychlé odeslání
23007-158	Fastons 6.3 x 0.8 mm	1	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE