

C-Profile Adaptor for Subracks Assembled into Cabinets



The C-profile, assembled on the Side Panel of the subrack serves to fix the subrack on the guiding profile when mounted into a cabinet.

CERTIFICATIONS



VLASTNOSTI

The C-profile fixes the subrack on the guiding profile when mounted into a cabinet.

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized
Produktová řada:	EuropacPRO
Product Type:	Telescopic Slide

Table 1/1

Katalogové číslo	Hloubka	Množství v balení	Works With	Rychlé odeslání
24562-453	175mm	2	Subracks	Ne
24562-454	235mm	2	Subracks	Ne
24562-455	295mm	2	Subracks	Ne

Katalogové číslo	Hloubka	Množství v balení	Works With	Rychlé odeslání
24562-456	355mm	2	Subracks	Ne
24562-457	415mm	2	Subracks	Ne
24562-458	475mm	2	Subracks	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Note: No end stop when pulling out the subrack.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE