


CPCI PlusIO Backplane



CompactPCI PlusIO combines the legacy CompactPCI and the new, high speed CompactPCI Serial Technology on one backplane. The CompactPCI PlusIO system slot addresses both, the parallel PCI bus as well as the CompactPCI Serial slots with PCIe, USB, Ethernet and S-ATA.

CERTIFICATIONS



VLASTNOSTI

In accordance with: PICMG 2.0 R3.0 CompactPCI Core Specification, PICMG 2.1 R2.0 Hot-Swap Specification, PICMG 2.9 R1.0 System Management Bus Specification, PICMG 2.10 R1.0 Keying Specification, PICMG 2.30 R1.0 CompactPCI PlusIO specification, PICMG CompactPCI Serial (CPCI-S.0 R1.0) specification

System slot in accordance with PICMG 2.30, 32-bit CPCI bus on P1, PCIe, S-ATA, USB & Ethernet on P2

CompactPCI peripheral slots, 32 bit with rear I/O on P2

Rear I/O on the CompactPCI Serial slots available on request

CompactPCI Serial peripheral slots with PCIe x1, S-ATA and USB

Full-mesh Ethernet on system slot and 2 CompactPCI Serial slots, supports 1000Base-T and 10GBase-T

V(I/O) can be set to 3.3 V or 5 V (preset to 5 V)

SPECIFIKACE

Table 1/3

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-602	Backplane	5	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-601	Backplane	8	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

Table 2/3

Katalogové číslo	Voltage I/O	Connector Type	Power Connector Type	Utility Connector Type	Šířka	Množství v balení
23007-602	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	102.2mm	1
23007-601	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	161.3mm	1

Table 3/3

Katalogové číslo	Rychlé odeslání
23007-602	Ne
23007-601	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE