

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

KATALOGOVÉ ČÍSLO

10630-048



Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the Online Configurator

VLASTNOSTI

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

VLASTNOSTI PRODUKTU

Product Type: Cabinet

Produktová řada: Varistar CP

Frame Material: Ocel

Povrchová úprava: Strukturovaný Práškový

Rack Height: 42U

Výška: 2000mm

Šířka: 600mm

Hloubka: 600mm

Static Load: 1600kg

Stupeň krytí: IP55

Complies With: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 Core Zone 4

Barva: Black Grey

Kód barvy: RAL 7021

Frequency: 50 Hz

Materiál: Ocel

Net Weight: 180.164kg

Množství v balení: 1

Shock and Vibration Tolerance: 5g (force)

Works With: Varistar CP

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE