

Varistar CP Seismic Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

KATALOGOVÉ ČÍSLO

10630-050



VLASTNOSTI

Earthquake secure up to Bellcore Zone 4, tested with 250 KGs per Telcordia GR-63 Core

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

VLASTNOSTI PRODUKTU

Product Type: Cabinet

Produktová řada: Varistar CP

Frame Material: Ocel

Rack Height: 42U

Výška: 2000mm

Šířka: 600mm

Hloubka: 600mm

Static Load: 1600kg

Stupeň krytí: IP55

Complies With: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 Core Zone 4

Barva: Black Grey

Kód barvy: RAL 7021

Povrchová úprava: Strukturovaný Práškový

Frequency: 50 Hz

Materiál: Ocel

Net Weight: 157.636kg

Množství v balení: 1

Shock and Vibration Tolerance: 5g (force)

Works With: Varistar CP

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE