


Aisle Containment Automatic Top Cover, 1200W 600D, RAL 7021

KATALOGOVÉ ČÍSLO

21130-592



Top cover that can be automatically opened in case of an event on site.

CERTIFICATIONS



VLASTNOSTI

Automatic containment top covers open automatically in the event of fire so that the facility sprinkler systems can put out the fire. In normal operation, the top covers are kept closed by electromagnets and open when the floating contact of the fire detection system is opened

Suitable for an aisle width of 1200 mm

Top cover with safety glass, 7 mm

With the universal top cover profile, the aisle height can be increased by 84 mm; please order separately

The top cover can be removed from the inside. When opened, the top cover provides access to lighting and sprinkler systems above the containment system for maintenance work

Please order the control unit, which can be used to control up to 12 automatic top covers, separately

A 24 VDC power supply unit is required to operate the system. Please order separately

VLASTNOSTI PRODUKTU

Šířka: 600mm

Hloubka: 1200mm

Množství v balení: 1

Barva: Black Grey

Kód barvy: RAL 7021

Povrchová úprava: Strukturovaný Práškový

Materiál: Ocel; Glass

Product Type: Cover

Typ: Aisle Top Cover, Automatic

Works With: Aisle Containment

DALŠÍ PODROBNOSTI O PRODUKTU

Please order the control unit, which can be used to control up to 12 automatic top covers, separately.

A 24 VDC power supply unit is required to operate the system. Please order separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE