

Rack Safety Plus, 3 U, 230 V AC, CEE

KATALOGOVÉ ČÍSLO

21270-005



The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

CERTIFICATIONS



VLASTNOSTI

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

400 V 3-phase or 230 V 1-phase mains input with mains fuses

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

VLASTNOSTI PRODUKTU

Product Type: Power Distributor

Works With: Varistar CP; Novastar

Function: Emergency Stop

Vstupní napětí AC: 230V

Počet fází: 1

EMC Filter: No

Surge Arrester: Yes

Inrush Current Limiter: No

Residual Current Device: Yes

Circuit Breaker Cover: Yes

Rack Height: 3U

Typ zásuvky: SCHUKO

Accessory Type: Power distribution accessories

Net Weight: 12kg

Množství v balení: 1

DALŠÍ PODROBNOSTI O PRODUKTU

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE