


# 19" Front Panel, 1 U, 3 mm, Al, Anodized, Untreated Edges

## KATALOGOVÉ ČÍSLO

**30219-098**



Front panels made of Aluminum.

## CERTIFICATIONS



## VLASTNOSTI

Aluminum, 4 or 3 mm thick, with Anodized or Painted finish

## VLASTNOSTI PRODUKTU

Rack Height: 1U

Hloubka (D): 3mm

Accessory Type: Front panel

Mounting: Screw-on Front

Povrchová úprava: Anodized

Front Finish: Anodized

Množství v balení: 1

Rear Finish: Anodized

Treated Edges: No

EMC Shielding: No

Výška (H): 43.6mm

Materiál: Hliník

Product Type: Front Panel

Rack Width: 95HP


Typ: 19" Front Panel

Šířka (W): 483mm

## DALŠÍ PODROBNOSTI O PRODUKTU

Please order 19" assembly kit separately.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:

[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE