


Socket Strip, SCHUKO, 3-Phase, 9 Sockets

KATALOGOVÉ ČÍSLO

60110-219



Modular, compact PDU with SCHUKO outlets and 3-phase connection.

CERTIFICATIONS



VLASTNOSTI

In accordance with DIN 57620

Socket strips with SCHUKO sockets, 3-phase

Connecting cable 2 m, open end with ferrules

3 phases, 16 A per phase

Socket strips can be rotated through all four directions (in 90° increments) during installation

Installation height 1 U

Vertical mounting

VLASTNOSTI PRODUKTU

Product Type: Socket Strip

Typ zásuvky: SCHUKO

Socket Quantity: 9

Barva: Grey; Black; Red

Switched Outlets: No

Length: 608.5mm

Napětí střídavé: 230V

Hloubka: 44mm

Povrchová úprava: Anodized

Materiál: Hliník; Polyamide

Net Weight: 1.65kg

Množství v balení: 1

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE