


EuropacPRO Cover Plate for Bolting to Side Panel



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

CERTIFICATIONS



VLASTNOSTI

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPECIFIKACE

Materiál:	Hliník
Product Type:	Cover Plate
Produktová řada:	EuropacPRO
Povrchová úprava:	Passivated
Typ:	Perforated
Works With:	Subracks

Table 1/1

Katalogové číslo	Rack Width	Hloubka	Množství v balení	Balení	Torque	Rychlé odeslání
------------------	------------	---------	-------------------	--------	--------	-----------------

24560-061	42HP	275mm	2	Pair		Ne
24560-062	63HP	275mm	2	Pair		Ne
24560-063	84HP	275mm	2	Pair		Ne
24560-064	42HP	175mm	2	Pair	2.1N·m	Ne
24560-065	42HP	235mm	2	Pair	2.1N·m	Ne
24560-066	42HP	295mm	2	Pair	2.1N·m	Ne
24560-071	63HP	175mm	2	Pair	2.1N·m	Ne
24560-072	63HP	235mm	2	Pair	2.1N·m	Ne
24560-073	63HP	295mm	2	Pair	2.1N·m	Ne
24560-078	84HP	175mm	2	Pair	2.1N·m	Ne
24560-079	84HP	235mm	2	Pair	2.1N·m	Ne
24560-080	84HP	295mm	2	Pair	2.1N·m	Ne
24560-081	84HP	355mm	2	Pair	2.1N·m	Ne
24560-082	84HP	415mm	2	Pair	2.1N·m	Ne
24560-083	84HP	475mm	2	Pair	2.1N·m	Ne
24579-090	42HP	277.75mm	2	Pair	2.1N·m	Ne
24579-092	84HP	277.75mm	2	Pair	2.1N·m	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit

selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE