


Fan Control Module FCM2



Management Module for Fan Control and Voltage Monitoring.

CERTIFICATIONS



VLASTNOSTI

The fan control module (FCM2) is a standalone fan controller for 12 V fans

Up to 6 fans can be monitored and controlled

Signal monitoring of up to 6 temperature sensors

Monitoring of 3.3 V, 5 V, 12 V and -12 V voltages

FCM2 supply voltage: 12 V

Can control status LEDs for Over Temp, Fan Fail, 3.3 V, 5 V, 12 V and -12 V

In case of overheating or the failure of a fan, the other fans can be set to full speed

Status information can be queried via I²C interface

Suitable for a 4 wire fan with PWM or control voltage input

SPECIFIKACE

Table 1/1

Katalogové číslo	Works With	Hloubka	Výška	Šířka	Množství v balení	Rychlé odeslání
23207-162	CompactPCI Systems	119mm	15mm	40mm	1	Ne

Katalogové číslo	Works With	Hloubka	Výška	Šířka	Množství v balení	Rychléodeslání
23207-160	CompactPCI Systems	119mm	15mm	40mm	1	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE