

Front Panel, Unshielded, With Fastener Pin



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICATIONS



VLASTNOSTI

Enable grounding of the front area (protection class 1)

SPECIFIKACE

Hloubka:	2.5mm
Rack Height:	3U
Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Typ:	Front Panel without Handle

Table 1/2

Katalogové číslo	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish	Treated Edges
20119-159	7HP	1	Screw-on Front	Anodized	Conductive	No

Katalogové číslo	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish	Treated Edges
20119-163	42HP	1	Screw-on Front	Anodized	Conductive	No
20119-162	28HP	1	Screw-on Front	Anodized	Conductive	No
20119-161	21HP	1	Screw-on Front	Anodized	Conductive	No
20119-160	14HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Katalogové číslo	Complies With	EMC Shielding	Výška	Šířka	Rychlé odeslání
20119-159	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	35.2mm	Ne
20119-163	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm	Ne
20119-162	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm	Ne
20119-161	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	106.3mm	Ne
20119-160	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	70.8mm	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE