


Novastar Raised Top Cover



Raised top cover for better ventilation and heat escape.
Novastar raised top cover is robust and not dismountable from the outside.

CERTIFICATIONS



VLASTNOSTI

Raised Top cover (31 mm) with all-round air gap of 10 mm

Top cover attached from the inside (no screws on the outside)

Suitable for placing heavy parts on the top cover

Incl. grounding

Robust version, load-carrying capacity 50 kg

SPECIFIKACE

Šířka:	553mm
Product Type:	Cabinet/Rack Top Cover
Materiál:	Ocel

Table 1/2

Katalogové číslo	Hloubka	Množství v balení	Barva	Kód barvy	Povrchová úprava	Typ
25230-037	800mm	1	Black Grey	RAL 7021	Strukturovaný Práškový	Raised

Katalogové číslo	Hloubka	Množství v balení	Barva	Kód barvy	Povrchová úprava	Typ
25230-142	1000mm	1	Black Grey	RAL 7021	Strukturovaný Práškový	Raised
25230-141	900mm	1	Black Grey	RAL 7021	Strukturovaný Práškový	Raised
25230-039	500mm	1	Black Grey	RAL 7021	Strukturovaný Práškový	Raised
25230-038	600mm	1	Black Grey	RAL 7021	Strukturovaný Práškový	Raised

Table 2/2

Katalogové číslo	Rychlé odeslání
25230-037	Ne
25230-142	Ne
25230-141	Ne
25230-039	Ne
25230-038	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order lifting eye separately if required.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE