


PCB Bracket



The PCB support brackets enable the fixing of a PCB to front panel. Available in different materials.



VLASTNOSTI

For fixing PCB to front panel

SPECIFIKACE

Product Type: Bracket
Works With: Front Panels
Typ: PCB Bracket

Table 1/2

Katalogové číslo	Materiál	Množství v balení	Flammability Rating	Hloubka	Výška	Šířka
60807-181	Zinc Alloy	1		8.6mm	11.1mm	10.2mm
60807-203	Zinc Alloy	1				
60807-183	Polybutylene Terephthalate	1	UL® 94V-0			
60807-011	Polybutylene Terephthalate	1	UL® 94V-0			
60807-211	Polybutylene Terephthalate	1	UL® 94V-0			

Table 2/2

Katalogové číslo	Thread Size	Thread Type	Rychlé odeslání
60807-181	M2.5	Metric	Ne
60807-203			Ne
60807-183			Ne
60807-011			Ne

Katalogové číslo	Thread Size	Thread Type	Rychlé odeslání
60807-211			Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Delivery is in standard pack multiples. Pricing is per individual item.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE