


PropacPRO Case Design Elements

To individualize the PropacPRO case design. The elements will be screwed from the rear side of the die cast frame.



CERTIFICATIONS



VLASTNOSTI

To individualize the case design

Available in 3 forms and two colors

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized
Works With:	Cases
Product Type:	Corner Profile
Produktová řada:	PropacPRO

Table 1/1

Katalogové číslo	Rack Width	Typ	Kód barvy	Barva	Rychlé odeslání
20850-190	42HP	Squared	RAL 7035	Light Grey	Ne
20850-184	42HP	Rounded	RAL 7035	Light Grey	Ne

Katalogové číslo	Rack Width	Typ	Kód barvy	Barva	Rychlé odeslání
20850-331	42HP	Triangle	RAL 5007	Brilliant Blue	Ne
20850-299	42HP	Rounded	RAL 5007	Brilliant Blue	Ne
20850-196	42HP	Triangle	RAL 7035	Light Grey	Ne
20850-191	63HP	Squared	RAL 7035	Light Grey	Ne
20850-332	63HP	Triangle	RAL 5007	Brilliant Blue	Ne
20850-315	42HP	Squared	RAL 5007	Brilliant Blue	Ne
20850-197	63HP	Triangle	RAL 7035	Light Grey	Ne
20850-300	63HP	Rounded	RAL 5007	Brilliant Blue	Ne
20850-301	84HP	Rounded	RAL 5007	Brilliant Blue	Ne
20850-185	63HP	Rounded	RAL 7035	Light Grey	Ne
20850-186	84HP	Rounded	RAL 7035	Light Grey	Ne
20850-198	84HP	Triangle	RAL 7035	Light Grey	Ne
20850-316	63HP	Squared	RAL 5007	Brilliant Blue	Ne
20850-317	84HP	Squared	RAL 5007	Brilliant Blue	Ne
20850-333	84HP	Triangle	RAL 5007	Brilliant Blue	Ne
20850-192	84HP	Squared	RAL 7035	Light Grey	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Size 28 HP and further colors available on request.

Cannot be combined with front hood.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE