


Varistar Mounting Plate



Varistar Mounting Plate for mounting electrical components and sub-assemblies, with 600 kg load capacity. The mounting plate can also be rear mounted and strengthening bracket can be added to increase load capacity.

CERTIFICATIONS



VLASTNOSTI

For mounting electrical components and sub-assemblies including cabling

Mounting pitch 25 mm in depth and 50 mm in height for partial-height mounting

Static load-carrying capacity up to 450 kg (rear mounted)

600 kg at full height, mounted to rear, with additional strengthening brackets

Strengthening bracket increases static load-carrying capacity

SPECIFIKACE

Product Type: Mounting Plate

Materiál: Ocel

Table 1/1

Katalogové číslo	Výška	Šířka	Množství v balení	Povrchová úprava	Rychlé odeslání
23130-405	1800mm	600mm	1	Pozinkovaná Ocel	Ne
23130-414	1200mm	800mm	1	Pozinkovaná Ocel	Ne
23130-413	1200mm	600mm	1	Pozinkovaná Ocel	Ne
23130-408	2000mm	800mm	1	Pozinkovaná Ocel	Ne
23130-406	1800mm	800mm	1	Pozinkovaná Ocel	Ne
23130-407	2000mm	600mm	1	Pozinkovaná Ocel	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Depth members are required for partial-height mounting.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE