


EuropacPRO Cover Plate, Universal



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be used is non-standard boards will be assembled into the subrack.

CERTIFICATIONS



VLASTNOSTI

Shielding is provided by optional EMC stainless steel gaskets, between cover plate and side panel

For variable positioning of horizontal rails e.g. for PCBs with non-standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPECIFIKACE

Materiál:	Hliník
Product Type:	Cover Plate
Produktová řada:	EuropacPRO
Povrchová úprava:	Passivated
Works With:	Subracks
Typ:	Universal

Table 1/1

Katalogové číslo	Rack Width	Hloubka	Množství v balení	Balení	Rychlé odeslání
24560-031	42HP	175mm	2	Pair	Ne

Katalogové číslo	Rack Width	Hloubka	Množství v balení	Balení	Rychlé odeslání
24560-032	42HP	235mm	2	Pair	Ne
24560-033	42HP	295mm	2	Pair	Ne
24560-041	63HP	175mm	2	Pair	Ne
24560-042	63HP	235mm	2	Pair	Ne
24560-043	63HP	295mm	2	Pair	Ne
24560-051	84HP	175mm	2	Pair	Ne
24560-052	84HP	235mm	2	Pair	Ne
24560-053	84HP	295mm	2	Pair	Ne
24560-054	84HP	355mm	2	Pair	Ne
24560-055	84HP	415mm	2	Pair	Ne
24560-056	84HP	475mm	2	Pair	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

In addition, 4 contact strips per subrack are required to affix cover to horizontal rail.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE