


EuropacPRO EMC Shielding Kit, Cover Plate to Horizontal Rail



Stainless steel gasket is clipped into a groove of horizontal rail and enables contact to the cover plate.

CERTIFICATIONS



VLASTNOSTI

Stainless steel gasket is clipped into horizontal rail and forms the contact cover plate

Fits all horizontal rails

SPECIFIKACE

Produktová řada:	EuropacPRO
Product Type:	Shielding Kit
Materiál:	Stainless Steel
Works With:	Sub racks

Table 1/1

Katalogové číslo	Rack Width	Množství v balení	Certifications	Rychlé odeslání
24560-241	42HP	10	RoHS	Ne
24560-243	63HP	10	RoHS	Ne

Katalogové číslo	Rack Width	Množství v balení	Certifications	Rychlé odeslání
24560-245	84HP	10	RoHS	Ne
24560-246	84HP	100	RoHS	Ne
24560-247	36HP	10		Ne

DALŠÍ PODROBNOSTI O PRODUKTU

When a rear hood is used, the stainless steel EMC gasket ensures the conductive connection between horizontal rail and rear hood.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE