


EuropacPRO Guide Rails to Accomodate Conduction Cooled Assemblies



The adapter is the interface between a subrack and the conduction cooled assemblies (CCAs).

CERTIFICATIONS



VLASTNOSTI

Adapter to hold conduction cooled assemblies (CCAs) in subracks

SPECIFIKACE

Materiál:	Hliník
Works With:	Subracks; Cases
Produktová řada:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO
Product Type:	Guide Rail

Table 1/2

Katalogové číslo	Typ	Množství v balení	Groove Width	Povrchová úprava	Length	Balení
24566-004	Conduction Cooled Assembly VPX	2	13.3	Passivated	160mm	Pair

Katalogové číslo	Typ	Množství v balení	Groove Width	Povrchová úprava	Length	Balení
24566-005	Conduction Cooled Assembly CompactPCI	2	13.3	Passivated	160mm	Pair

Table 2/2

Katalogové číslo	Rychlé odeslání
24566-004	Ne
24566-005	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Suitable for heavy and rugged horizontal rails.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE