


nVent CADDY Pyramid ST Bridge Assembly



FUNKTIONER

Ideal for supporting multiple pipe runs, cable tray and air handling units

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance

SPECIFIKATIONER

Static Load Safety Factor: 3:1

Finish: Hot-Dip Galvanized

Temperature: -45 to 65 °C

Table 1/2

Katalognummer	Artikelnummer	Materiale	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)
PSB24A	360475	Polyethylene, Polypropylene, Stål	610 mm	673 mm	142 mm	203 mm
PSB36A	360477	Polyethylene, Polypropylene, Stål	914 mm	978 mm	142 mm	203 mm

Katalognummer	Artikelnummer	Materiale	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)
PSB42A	360478	Polyethylene, Polypropylene, Stål	1067 mm	1143 mm	142 mm	203 mm

Table 2/2

Katalognummer	Artikelnummer	Surface Area	Unit Weight	Static Load
PSB24A	360475	118709mm ²	2 kg	8900N
PSB36A	360477	118709mm ²	4 kg	8900N
PSB42A	360478	183225mm ²	4 kg	13340N

YDERLIGERE PRODUKTOPLYSNINGER

Static loads are assumed to be uniformly distributed.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

