

Interscale Desktop Case, Non-Perforated



Flexible desktop case with integrated EMC protection.
Based on the nVent SCHROFF Interscale platform and
developed in accordance with IEC 60297-3-109.

CERTIFICATIONS



VLASTNOSTI

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases upon request

SPECIFIKACE

Materiál:	Hliník; Ocel
Typ:	Desktop
Produktová řada:	Interscale
Stupeň krytí:	IP30
Kód barvy:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Katalogové číslo	Výška	Množství v balení	Šířka	Hloubka	Cooling	Barva
14820-133	43.7mm	1	132.6mm	132.6mm	Non-Perforated	Anthracite Grey
14820-134	43.7mm	1	133mm	177mm	Non-Perforated	Anthracite Grey
14820-154	43.7mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-254	88.1mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-155	43.7mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-175	43.7mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-195	43.7mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-197	43.7mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-255	88.1mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-275	88.1mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-295	88.1mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-297	88.1mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-375	132.6mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-395	132.6mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-397	132.6mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey

Table 2/2

Katalogové číslo	Povrchová úprava	Rychlé odeslání
14820-133	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne

Katalogové číslo	Povrchová úprava	Rychlé odeslání
14820-134	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-154	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-254	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-155	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-175	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-195	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-197	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-255	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-275	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-295	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-297	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-375	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-395	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne
14820-397	Aluminum-Zinc Plated, Strukturovaný Práškový	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE