


# Interscale Flexible Rail System for Mounting PCBs



Interscale flexible rail system for mounting PCBs in Interscale SFF Cases. Supports individual mounting of PCBs in combination with a mounting plate.

## VLASTNOSTI

Board support is bolted onto mounting plate

PCB (board thickness 1.4 ... 2.6 mm) can be positioned flexibly

## SPECIFIKACE

|                          |                         |
|--------------------------|-------------------------|
| <b>Materiál:</b>         | Hliník                  |
| <b>Povrchová úprava:</b> | Anodized                |
| <b>Produktová řada:</b>  | Interscale              |
| <b>Product Type:</b>     | Mounting Kit            |
| <b>Typ:</b>              | Mounting Kit            |
| <b>Works With:</b>       | Small Form Factor Cases |

Table 1/1

| Katalogové číslo | Length   | Množství v balení | Rychlé odeslání |
|------------------|----------|-------------------|-----------------|
| 24827-023        | 128.55mm | 2                 | Ne              |
| 24827-024        | 173mm    | 2                 | Ne              |
| 24827-025        | 217.45mm | 2                 | Ne              |
| 24827-027        | 306.35mm | 2                 | Ne              |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**