

Interscale for Mini-ITX, Conduction Cooled



Small form factor case with integrated EMC-shielding and conduction cooling for Mini-ITX boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICATIONS



VLASTNOSTI

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Cutout for Mini ITX I/O panel, power connector (Phoenix Contact, 0710028) and power switch (Schurter, MCS 18 Front)

Integrated EMC protection

Other dimensions, cutout shapes or locations, and screen printing available

Rigid construction requires only four screws

Board mounting studs installed

Color RAL 7016

SPECIFIKACE

Výška:	94mm
Hloubka:	189mm
Materiál:	Hliník
Typ:	Desktop
Produktová řada:	Interscale
Stupeň krytí:	IP30
Kód barvy:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Katalogové číslo	Design Feature	Množství v balení	Cooling	Barva	Povrchová úprava	Šířka
14830-005	10 mm Fins	1	Conduction Cooled	Anthracite Grey	Strukturovaný Práškový	184mm
14830-006	20 mm Fins	1	Conduction Cooled	Anthracite Grey	Strukturovaný Práškový	184mm

Table 2/2

Katalogové číslo	Rychlé odeslání
14830-005	Ne
14830-006	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE