


# MultipacPRO Front Handle, One-Piece, Width 10 mm



The front handles can be mounted and provide an easier to mount assembly. The handles can be assembled from the front side.

## CERTIFICATIONS



## VLASTNOSTI

Load-carrying capacity 30 kg/pair

Assembly on the front panel

Can be used for the aluminium or sheet metal versions

## SPECIFIKACE

|                          |                                      |
|--------------------------|--------------------------------------|
| <b>Materiál:</b>         | Hliník                               |
| <b>Povrchová úprava:</b> | Anodized                             |
| <b>Works With:</b>       | Chassis; Front Panels                |
| <b>Produktová řada:</b>  | MultipacPRO; Frame Type Plug-In Unit |
| <b>Product Type:</b>     | Handle                               |

Table 1/1

| Katalogové číslo | Rack Height | Množství v balení | Typ rukojeti | Barva  | Šířka | Rychlé odeslání |
|------------------|-------------|-------------------|--------------|--------|-------|-----------------|
| 20860-256        | 1U          | 2                 | Straight     | Silver | 10mm  | Ne              |
| 20860-257        | 2U          | 2                 | Straight     | Silver | 10mm  | Ne              |

| Katalogové číslo | Rack Height | Množství v balení | Typ rukojeti | Barva  | Šířka | Rychléodeslání |
|------------------|-------------|-------------------|--------------|--------|-------|----------------|
| 20860-258        | 3U          | 2                 | Straight     | Silver | 10mm  | Ne             |
| 20860-259        | 4U          | 2                 | Straight     | Silver | 10mm  | Ne             |
| 20860-260        | 5U          | 2                 | Straight     | Silver | 10mm  | Ne             |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**