

Speedway Cable Ladder Inside Riser, 45°



CERTIFICERINGER



FUNKTIONER

Creates a 45° inside riser elevation change for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

SPECIFIKATIONER

Finish: Hot-Dip Galvanized

Materiale: Stål

Table 1/2


Katalognummer	Artikelnummer	Width (W)	Angle (a)	A	B	C
---------------	---------------	-----------	-----------	---	---	---

CL110X750IR45 HD	840340	750 mm	45 °	286 mm	193 mm	290 mm
CL110X150IR45 HD	840300	150 mm	45 °	286 mm	193 mm	290 mm
CL110X600IR45 HD	840330	600 mm	45 °	286 mm	193 mm	290 mm
CL110X450IR45 HD	840320	450 mm	45 °	286 mm	193 mm	290 mm
CL110X900IR45 HD	840350	900 mm	45 °	286 mm	193 mm	290 mm
CL110X300IR45 HD	840310	300 mm	45 °	286 mm	193 mm	290 mm

Table 2/2

Katalognummer	Artikelnummer	D
CL110X750IR45HD	840340	80 mm
CL110X150IR45HD	840300	80 mm
CL110X600IR45HD	840330	80 mm
CL110X450IR45HD	840320	80 mm
CL110X900IR45HD	840350	80 mm
CL110X300IR45HD	840310	80 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

