


Panhead Screw, Torx, Self-Tapping

Panhead screws.



CERTIFICATIONS



VLASTNOSTI

Panhead screw with torx, self-forming

For mounting trapezoid handles to the front panel of PRO frame-type plug-in units

SPECIFIKACE

Typ:	Panhead Screw
Product Type:	Screw
Materiál:	Ocel
Povrchová úprava:	Pozinkovaná Ocel

Table 1/2

Katalogové číslo	Length	Množství v balení	Thread Size	Produktová řada	Works With	Torque
24560-157	7.3mm	100	M2.5		Front Panels	
24560-141	9.3mm	100	M2.5	Frame Type Plug-In Unit	Guide Rails	

Katalogové číslo	Length	Množství v balení	Thread Size	Produktová řada	Works With	Torque
24560-179	10mm	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Subracks, Cases, Chassis	
21101-884	6mm	100	M4	EuropacPRO	Subracks	1.3N·m

Table 2/2

Katalogové číslo	Rychlé odeslání
24560-157	Ne
24560-141	Ne
24560-179	Ne
21101-884	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE