


RatiopacPRO AIR Radial Fan Unit



Simple mountable radial Fan Unit for RatiopacPRO AIR, with a air capacity of 36 m³/h (free blowing) per fan. Available in 4 widths and 2 depths and with up to 3 fans equipped.

CERTIFICATIONS



VLASTNOSTI

Ball-bearing radial fans

Air capacity 36 m³/h (free blowing) per fan

Fits for RatiopacPRO Air cases (fan unit needs only 0,5 U height)

Only 1/2 U height

Air exhaust via perforation in cover plate

No restriction to rear mounting space

No mechanical modification of the case necessary

Simple mounting

SPECIFIKACE

Materiál:	Hliník
Works With:	Cases
Product Type:	Fan
Typ:	Radial Fan
Produktová řada:	RatiopacPRO AIR

Table 1/1

Katalogové číslo	Rack Width	Napětí stejnosměrné	Průtok vzduchu	Hloubka	Šířka	Rychlé odeslání
------------------	------------	---------------------	----------------	---------	-------	-----------------

24572-408	28HP	12V	36m³/h	220mm	146.87mm	Ne
24572-405	42HP	12V	36m³/h	160mm	218mm	Ne
24572-409	42HP	12V	36m³/h	220mm	218mm	Ne
24572-406	63HP	12V	36m³/h	160mm	324.67mm	Ne
24572-410	63HP	12V	36m³/h	220mm	324.67mm	Ne
24572-407	84HP	12V	36m³/h	160mm	431.35mm	Ne
24572-411	84HP	12V	36m³/h	220mm	431.35mm	Ne
24572-404	28HP	12V	36m³/h	160mm	146.87mm	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE