

Varistar CP Cross Member



Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load. The hole pattern allows easy reccessment of the 19" plane in 25 mm increments.

VLASTNOSTI

Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load

Hole pattern allows easy reccessment of the 19" plane in 25 mm increments

SPECIFIKACE

Table 1/2

Katalogové číslo	Works With	Materiál	Povrchová úprava	Barva	Kód barvy	Hloubka
24630-214	Varistar CP	Ocel	Strukturovaný Práškový	Black Grey	RAL 7021	900mm
24630-213	Varistar CP	Ocel	Strukturovaný Práškový	Black Grey	RAL 7021	800mm
24630-212	Varistar CP	Ocel	Strukturovaný Práškový	Black Grey	RAL 7021	600mm

Table 2/2

Katalogové číslo	Množství v balení	Balení	Rychlé odeslání
24630-214	4	Pair	Ne
24630-213	4	Pair	Ne
24630-212	4	Pair	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE