


Varistar CP Seismic Base Plate, IP55 and EMC, One-Piece

The base plate is solid and covers the base of the cabinet.



VLASTNOSTI

The base plate is solid and covers the base of the cabinet

Is assembled from outside

SPECIFIKACE

Product Type:	Cabinet/Rack Base
Povrchová úprava:	Hot-Dip Galvanized
Stupeň krytí:	IP55
Materiál:	Ocel

Table 1/2

Katalogové číslo	Šířka	Hloubka	Množství v balení	Complies With	Typ	Works With
20630-309	600mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-310	600mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP

Katalogové číslo	Šířka	Hloubka	Množství v balení	Complies With	Typ	Works With
20630-311	600mm	1000mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-312	600mm	1200mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-313	800mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-314	800mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-315	800mm	1000mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP
20630-316	800mm	1200mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP

Table 2/2

Katalogové číslo	Rychlé odeslání
20630-309	Ne
20630-310	Ne
20630-311	Ne
20630-312	Ne
20630-313	Ne
20630-314	Ne
20630-315	Ne

Katalogové číslo	Rychlé odeslání
20630-316	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE