


Speedway Cable Ladder Outside Riser, 90°



CERTIFICERINGER



FUNKTIONER

Creates a 90° outside riser elevation change for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

SPECIFIKATIONER

Finish: Hot-Dip Galvanized

Materiale: Stål

Table 1/2


Katalognummer	Artikelnummer	Width (W)	Angle (a)	A	B	C
---------------	---------------	-----------	-----------	---	---	---

CL110X900OR9 OHD	840650	900 mm	90 °	410 mm	410 mm	580 mm
CL110X750OR9 OHD	840640	750 mm	90 °	410 mm	410 mm	580 mm
CL110X600OR9 OHD	840630	600 mm	90 °	410 mm	410 mm	580 mm
CL110X450OR9 OHD	840620	450 mm	90 °	410 mm	410 mm	580 mm
CL110X150OR9 OHD	840600	150 mm	90 °	410 mm	410 mm	580 mm
CL110X300OR9 OHD	840610	300 mm	90 °	410 mm	410 mm	580 mm

Table 2/2

Katalognummer	Artikelnummer	D
CL110X900OR90HD	840650	80 mm
CL110X750OR90HD	840640	80 mm
CL110X600OR90HD	840630	80 mm
CL110X450OR90HD	840620	80 mm
CL110X150OR90HD	840600	80 mm
CL110X300OR90HD	840610	80 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

