

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Data Solutions



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FUNKTIONER

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFIKATIONER

Locking Type:	3-Point Locking
Product Type:	Cabinet Door
Beskyttelsesgrad:	IP55
Materiale:	Stål

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Pakke mængde	Farve	Farvekode
21630-171	47U	2200mm	800mm	1	Black Grey	RAL 7021
21630-210	24U	1200mm	600mm	1	Black Grey	RAL 7021
21630-211	29U	1400mm	600mm	1	Black Grey	RAL 7021

Katalognummer	Rack Height	Højde	Bredde	Pakke mængde	Farve	Farvekode
21630-212	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-213	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-214	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-215	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-216	24U	1200mm	800mm	1	Black Grey	RAL 7021
21630-217	29U	1400mm	800mm	1	Black Grey	RAL 7021
21630-218	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-219	38U	1800mm	800mm	1	Black Grey	RAL 7021
21630-220	42U	2000mm	800mm	1	Black Grey	RAL 7021

Table 2/2

Katalognummer	Complies With	Finish	Type	Works With
21630-171	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-210	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-211	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-212	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-213	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-214	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-215	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-216	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP

Katalognummer	Complies With	Finish	Type	Works With
21630-217	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-218	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-219	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-220	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP

YDERLIGERE PRODUKTOPLYSNINGER

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE