

# Ejection Stop Kit



## CERTIFICERINGER



## FUNKTIONER

Holds nVent ERIFLEX Flexibar laminates in place while punch is raised

Pressure plates notched to apply pressure to laminates without damaging the insulation

Punch tip remains visible when kit is attached to puncher

RoHS compliant

## SPECIFIKATIONER

Table 1/1

| Katalognummer  | Artikelnummer | Product                            | Materiale        | Punch Size                                            | Unit Weight |
|----------------|---------------|------------------------------------|------------------|-------------------------------------------------------|-------------|
| EJECSTOP18-20S | 545896        | Replacement Ejection Stop          | Elastomere       | 18.0 mm, 20.0 mm                                      | 0.06 kg     |
| EJECSTOP6-14S  | 545895        | Replacement Ejection Stop          | Elastomere       | 6.5 mm, 9.0 mm, 11.0 mm, 14.0 mm, 5/16", 3/8", 17/32" | 0.07 kg     |
| EJECSTOP18-20L | 545894        | Ejection Stop with Pressure Plates | Stål, Elastomere | 18.0 mm, 20.0 mm                                      | 0.28 kg     |

| Katalognummer | Artikelnummer | Product                                       | Materiale        | Punch Size                                            | Unit Weight |
|---------------|---------------|-----------------------------------------------|------------------|-------------------------------------------------------|-------------|
| EJECSTOP6-14L | 545893        | Ejection Stop with Pressure Plates and Washer | Stål, Elastomere | 6.5 mm, 9.0 mm, 11.0 mm, 14.0 mm, 5/16", 3/8", 17/32" | 0.55 kg     |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**