

LED-lamper til farlige lokationer, LEDHL



Hazardous Location LED Strip Lights provide enclosure illumination in hazardous environments. These lights are ideal for remote and darkened enclosure applications in Class 1, Division 2 hazardous areas. With a robust design, these lights have a life span of 100,000 hours and superior lighting performance with easy field angle adjustment brackets. These versatile, light-weight LED lights provide mounting flexibility and are easy to install in an enclosure.

INDUSTRISTANDARDER

UL 844 Listed; File No. E492323

cUL Listed per CSA C22.2 No. 137; File No. E492323

Class I, Division 2 Groups A, B, C, D, T4*; Class II, Division 2, Groups F, and G, T6; Class III; Class I, Zone 2, Group IIC; Zone 22

IEC 60529, IP66/67

*T3C for simultaneous exposure rating, Class I Div. 2 & Class II, Div.

2

FUNKTIONER

Direct transfer of heat from PCB to the casing to maximize lifetime and reliability

Operating temperature of -40 F (-40 C) to 140 F (60 C)

Easy installation with included mechanical assembly kit while maintaining enclosure rating up to UL Type 4X

Includes 3-ft connect cable with flying leads

Maximum lighting for control panels with 578 to 2,351 lumens and 5,000K color temperature

Linear drive circuit with no flicker or high frequency electronic noise

Easy field angle adjustment with mounting bracket

Wide beam optics with 100 degree angle of illumination

Available in 12, 24, 36, and 48-inch lengths

SPECIFIKATIONER

Table 1/1						
Katalognummer	Materiale	Finish	Indgangsspænding DC	Current	Light Output	Hurtigforsendelse
LEDHL24V12	Aluminium	Poleret	22 – 28V	0.4A	578lm	Nej
LEDHL24V24	Aluminium	Poleret	22 – 28V	0.75A	1172lm	Nej
LEDHL24V36	Aluminium	Poleret	22 – 28V	1.1A	1758lm	Nej
LEDHL24V48	Aluminium	Poleret	22 – 28V	1.5A	2351lm	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE