

EB-60 Earthing and Neutral Busbar



nVent ERIFLEX Connecting, Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, for wind and solar power generation and in data centers.

CERTIFICERINGER



FUNKTIONER

Use to connect several earthing conductors within a panel

Chamfered holes allow for easy connections

Mounting slots for universal fixing to copper busbar, directly to rails or spacers

Rigid bar

Mounting kits available for stacking busbars or fixing to DIN rail


RoHS compliant

SPECIFIKATIONER

Katalognummer	EB60
Artikelnummer	568661
Materiale	Brass
Number of Connections	60
Conductor Size, IEC	(1) 16 - 35 mm ² Stranded (1) 4 - 16 mm ² Stranded (58) 1.5 - 4 mm ² Stranded

Katalognummer	EB60
Ferrule Conductor Size, IEC	(1) 10 - 35 mm ² (1) 2.5 - 16 mm ² (58) 0.75 - 4 mm ²
Conductor Size, UL	(1) #6 Stranded (1) #12 - #6 Stranded (58) #16 - #10 Stranded (58) #16 - #10 Solid
Max Current Rating	250A
Dybde (D)	13mm
Height (H)	13 mm
Width (W)	462 mm
Thickness (T)	5 mm
A	376 mm
B	43 mm
X	6.2 x 7 mm
Unit Weight	0.31 kg
Complies With	IEC® 61439.1

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE