We connect and protect

H2Omit-udluftningsdræn

H2Omit Vent Drains allow accumulated water to drain out the bottom of an enclosure. The UL-approved vent drains also function as an air pressure equalizer, reducing the harmful effects of temperature-induced vacuums that could pull water and moisture into the enclosure.

INDUSTRISTANDARDER

UL 508A Listed; Type 4, 4X; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X; File No. E61997

Maintains UL/cUL Type 4, 4X rating when properly installed on a UL/cUL Type 4 or 4X enclosure.

NEMA/EEMAC Type 4, 4X

IEC 60529, IPx6

FUNKTIONER

En envejs, mekanisk lukkeanordning, som ved trykudligning forhindrer vand og forurenende stoffer i at trænge ind i skabet
Medvirker til at reducere korrosion, der kan begrænse de elektriske og elektroniske komponenters levetid
Uses gravity to remove collected liquids
Installs in a 7/8-inch hole in the bottom of enclosure with provided nut or in a 1/2-inch NPT/NPS threaded conduit hub
Installs in the bottom of mild steel, aluminum, stainless steel or non-metallic enclosures
Maintains the enclosure UL Type rating when properly installed
Stainless Steel Vent Drain
Corrosion-resistant polyester material with a Type 304 stainless steel sleeve
Non-Metallic Drain Vent
Corrosion-resistant polyester material
2.00-inch long x 1.25-inch outside diameter

SPECIFIKATIONER

Table 1/1

Katalognummer	Højde	Bredde	Dybde	Materiale	Finish	Farve
AVDR4NM	67mm	32mm	32mm	Polyester	Smooth Matte	Gray
AVDR4SS4	67mm	35mm	35mm	Stainless Steel 304	Poleret	

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.