

# Internal side panels | Strømfordeling, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

## FUNKTIONER

Beskrivelse: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Materiale: 1.5 mm galvanized steel.

Levering inkluderer: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

## SPECIFIKATIONER

**Tykkelse:** 1.5mm  
**Finish:** Galvaniseret  
**Materiale:** Stål

Table 1/1

Katalognummer	Højde	Bredde	Dybde	Panelstørrelse	Enclosure Material	Produktfamilie
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Lakeret Stål	Free-Standing
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Lakeret Stål	Free-Standing
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Lakeret Stål	Free-Standing
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Lakeret Stål	Free-Standing
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Lakeret Stål	Free-Standing
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Lakeret Stål	Free-Standing
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Lakeret Stål	Free-Standing
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Lakeret Stål	Free-Standing
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Lakeret Stål	Free-Standing
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Lakeret Stål	Free-Standing
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Lakeret Stål	Free-Standing
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Lakeret Stål	Free-Standing
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Lakeret Stål	Free-Standing
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Lakeret Stål	Free-Standing
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Lakeret Stål	Free-Standing
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Lakeret Stål	Free-Standing

Katalognummer	Højde	Bredde	Dybde	Panelstørrelse	EnclosureMaterial	Produktfamilie
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Lakeret Stål	Free-Standing
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Lakeret Stål	Free-Standing

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**