

# BEP Bar End Protector



Bar end protectors are placed onto the ends of threaded reinforcing steel bars. These protective caps help prevent damage to the nVent LENTON threads and help keep dirt and water out of the threads during storage, transportation and installation.

## FUNKTIONER

Easy to install and remove

Color coded for the appropriate reinforcing bar size

## SPECIFIKATIONER

Table 1/1

| Katalognummer | Artikelnummer | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Farve  |
|---------------|---------------|--------------------|----------------|--------------------|--------|
| EL10BTP       | 370000        | 10 mm              | #3             |                    | Yellow |
| EL12BTP       | 370010        | 12 mm              | #4             | 10M                | Red    |
| EL14BTP       | 370020        | 14 mm              |                |                    | Green  |
| EL16BTP       | 370060        | 16 mm              | #5             | 15M                | Black  |
| EL18BTP       | 370130        | 18 mm              |                |                    | White  |
| EL20BTP       | 370070        | 20 mm              | #6             | 20M                | Yellow |
| EL22BTP       | 370140        | 22 mm              | #7             |                    | Blue   |

| Katalognummer | Artikelnummer | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Farve  |
|---------------|---------------|--------------------|----------------|--------------------|--------|
| EL25BTP       | 370080        | 25 mm              | #8             | 25M                | Red    |
| EL28BTP       | 370090        | 28 mm              | #9             | 30M                | Black  |
| EL30BTP       | 370100        | 30 mm              |                |                    | White  |
| EL32BTP       | 370150        | 32 mm              | #10            |                    | Yellow |
| EL34BTP       | 370160        | 34 mm              |                |                    | Red    |
| EL36BTP       | 370110        | 36 mm              | #11            | 35M                | Blue   |
| EL38BTP       | 370170        | 38 mm              | #12            |                    | White  |
| EL40BTP       | 370120        | 40 mm              |                |                    | Green  |
| EL43TBTP      | 370180        | 43 mm              | #14            | 45M                | Red    |
| EL50TBTP      | 370190        | 50 mm              |                |                    | Black  |
| EL57TBTP      | 370200        | 57 mm              | #18            | 55M                | Blue   |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**