


Front Handle One-Piece, Width 12.2 mm

Power Utilities



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Pakke mængde	Håndtagstype	Farve	Materiale	Produktfamilie
10501-116	1 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-029	6 U	1	Straight	Black	Aluminium	EuropacPRO
10501-022	6 U	1	Angled Handle	Silver	Aluminium	EuropacPRO

Katalognummer	Rack Height	Pakke mængde	Håndtagstype	Farve	Materiale	Produktfamilie
10501-008	6 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-007	5 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-016	2 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-006	4 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-021	4 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-005	3 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-018	4 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-025	2 U	1	Straight	Black	Aluminium	EuropacPRO
10501-026	3 U	1	Straight	Black	Aluminium	EuropacPRO
10501-020	3 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-027	4 U	1	Straight	Black	Aluminium	EuropacPRO
10501-004	2 U	1	Straight	Silver	Aluminium	EuropacPRO
10501-028	5 U	1	Straight	Black	Aluminium	EuropacPRO

Table 2/2

Katalognummer	Product Type	Works With	Torque
10501-116	Handle	Subracks	
10501-029	Handle	Subracks	2.4 N·m
10501-022	Handle	Subracks	2.4 N·m
10501-008	Handle	Subracks	2.4 N·m

Katalognummer	Product Type	Works With	Torque
10501-007	Handle	Subracks	
10501-016	Handle	Subracks	
10501-006	Handle	Subracks	
10501-021	Handle	Subracks	2.4 N·m
10501-005	Handle	Subracks	2.4 N·m
10501-018	Handle	Subracks	2.4 N·m
10501-025	Handle	Subracks	
10501-026	Handle	Subracks	2.4 N·m
10501-020	Handle	Subracks	2.4 N·m
10501-027	Handle	Subracks	
10501-004	Handle	Subracks	
10501-028	Handle	Subracks	

YDERLIGERE PRODUKTOPLYSNINGER

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE