

Front Panel, Flat, Unshielded, D-Sub Cutouts

Power Utilities



Flat front panel with cutout for D-Sub connectors.
Unshielded version.

CERTIFICERINGER



FUNKTIONER

Non-shielded version

Aluminum, 2.5 mm, front anodized, rear conductive

SPECIFIKATIONER

Table 1/3

Katalognummer	Pakke mængde	Mounting	Front Finish	Rear Finish	Treated Edges	Complies With
30118-346	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10

Katalognummer	Pakke mængde	Mounting	Front Finish	Rear Finish	Treated Edges	Complies With
30118-344	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-345	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-347	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-341	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-343	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-342	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10

Table 2/3

Katalognummer	EMC Shielding	Højde	Materiale	Product Type	Rack Height	Rack Width
30118-346	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-344	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-345	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-347	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-341	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-343	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP
30118-342	No	128.4 mm	Aluminium	Front Panel	3 U	4 HP

Table 3/3

Katalognummer	Type	Bredde
30118-346	Front Panel without Handle	20 mm

Katalognummer	Type	Bredde
30118-344	Front Panel without Handle	20 mm
30118-345	Front Panel without Handle	20 mm
30118-347	Front Panel without Handle	20 mm
30118-341	Front Panel without Handle	20 mm
30118-343	Front Panel without Handle	20 mm
30118-342	Front Panel without Handle	20 mm

YDERLIGERE PRODUKTOPLYSNINGER

Delivery is in standard pack multiples. Pricing is per individual item.

Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE