


# Novastar Frame, Slim-Line

## Power Utilities



Aesthetic aluminum die-cast frame with 200kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

## CERTIFICATIONS



## FEATURES

Static load-carrying capacity 200 kg

19" plane - 33 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height | Width | Depth | Color | Color Code |
|----------------|-------------|--------|-------|-------|-------|------------|
|----------------|-------------|--------|-------|-------|-------|------------|

|           |      |        |        |         |            |          |
|-----------|------|--------|--------|---------|------------|----------|
| 28230-001 | 6 U  | 323 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-060 | 6 U  | 323 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-004 | 9 U  | 456 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-063 | 9 U  | 456 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-007 | 12 U | 589 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-054 | 12 U | 589 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-055 | 12 U | 589 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-066 | 12 U | 589 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-126 | 12 U | 589 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-011 | 16 U | 767 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-070 | 16 U | 767 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-130 | 16 U | 767 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-190 | 16 U | 767 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-191 | 16 U | 767 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-015 | 20 U | 945 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-074 | 20 U | 945 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-134 | 20 U | 945 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-194 | 20 U | 945 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-195 | 20 U | 945 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |

|           |      |         |        |         |            |          |
|-----------|------|---------|--------|---------|------------|----------|
| 28230-020 | 25 U | 1167 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-079 | 25 U | 1167 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-139 | 25 U | 1167 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-198 | 25 U | 1167 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-199 | 25 U | 1167 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-029 | 34 U | 1567 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-088 | 34 U | 1567 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-148 | 34 U | 1567 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-202 | 34 U | 1567 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-203 | 34 U | 1567 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-033 | 38 U | 1745 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-092 | 38 U | 1745 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-152 | 38 U | 1745 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-206 | 38 U | 1745 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-207 | 38 U | 1745 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-048 | 43 U | 1967 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-097 | 43 U | 1967 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-157 | 43 U | 1967 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-210 | 43 U | 1967 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |

|           |      |         |        |         |            |          |
|-----------|------|---------|--------|---------|------------|----------|
| 28230-211 | 43 U | 1967 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |
| 28230-042 | 47 U | 2145 mm | 553 mm | 500 mm  | Black Grey | RAL 7021 |
| 28230-101 | 47 U | 2145 mm | 553 mm | 600 mm  | Black Grey | RAL 7021 |
| 28230-162 | 47 U | 2145 mm | 553 mm | 800 mm  | Black Grey | RAL 7021 |
| 28230-214 | 47 U | 2145 mm | 553 mm | 900 mm  | Black Grey | RAL 7021 |
| 28230-215 | 47 U | 2145 mm | 553 mm | 1000 mm | Black Grey | RAL 7021 |

| Table 2/2      |                |                    |             |           |
|----------------|----------------|--------------------|-------------|-----------|
| Catalog Number | Frame Material | Product Type       | Static Load | Type      |
| 28230-001      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-060      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-004      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-063      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-007      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-054      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-055      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-066      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-126      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-011      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-070      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-130      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |

| Catalog Number | Frame Material | Product Type       | Static Load | Type      |
|----------------|----------------|--------------------|-------------|-----------|
| 28230-190      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-191      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-015      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-074      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-134      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-194      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-195      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-020      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-079      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-139      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-198      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-199      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-029      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-088      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-148      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-202      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-203      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-033      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |

| Catalog Number | Frame Material | Product Type       | Static Load | Type      |
|----------------|----------------|--------------------|-------------|-----------|
| 28230-092      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-152      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-206      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-207      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-048      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-097      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-157      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-210      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-211      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-042      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-101      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-162      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-214      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |
| 28230-215      | Aluminum       | Cabinet/Rack Frame | 200 kgf     | Slim-Line |

## ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**