

Varistar CP Base/Plinth Side

Power Utilities

Sides trim to mount to Varistar CP base/plinth

FEATURES

Base/plinth sides, plain

SPECIFICATIONS

Table 1/2

Catalog Number	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-038	100 mm	1000 mm	1	Black Grey	RAL 7021	Powder Coated
24630-039	100 mm	1100 mm	1	Black Grey	RAL 7021	Powder Coated
24630-040	100 mm	1200 mm	1	Black Grey	RAL 7021	Powder Coated
24630-041	200 mm	1000 mm	1	Black Grey	RAL 7021	Powder Coated
24630-042	200 mm	1100 mm	1	Black Grey	RAL 7021	Powder Coated
24630-043	200 mm	1200 mm	1	Black Grey	RAL 7021	Powder Coated
24630-077	100 mm	600 mm	1	Black Grey	RAL 7021	Powder Coated
24630-078	100 mm	800 mm	1	Black Grey	RAL 7021	Powder Coated
24630-079	100 mm	900 mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-080	200 mm	600 mm	1	Black Grey	RAL 7021	Powder Coated
24630-081	200 mm	800 mm	1	Black Grey	RAL 7021	Powder Coated
24630-082	200 mm	900 mm	1	Black Grey	RAL 7021	Powder Coated
24630-083	100 mm	300 mm		Black Grey	RAL 7021	Powder Coated
24630-084	200 mm	300 mm		Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Material	Product Type	Type	Package Unit
24630-038	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-039	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-040	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-041	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-042	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-043	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-077	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-078	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-079	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-080	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-081	Steel	Cabinet/Rack Base	Plinth Side	Pair
24630-082	Steel	Cabinet/Rack Base	Plinth Side	Pair

Catalog Number	Material	Product Type	Type	Package Unit
24630-083	Steel	Cabinet/Rack Base	Plinth Side	
24630-084	Steel	Cabinet/Rack Base	Plinth Side	

ADDITIONAL PRODUCT DETAILS

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE