

Novastar Frame, Heavy-Duty

Power Utilities



Aesthetic aluminum die-cast frame with 400 kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 400 kg

19" plane - 60 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Depth	Color	Color Code
----------------	-------------	--------	-------	-------	-------	------------

28230-056	12 U	589 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-189	12 U	589 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-192	16 U	767 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-193	16 U	767 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-310	16 U	767 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-370	16 U	767 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-430	16 U	767 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-196	20 U	945 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-197	20 U	945 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-314	20 U	945 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-374	20 U	945 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-434	20 U	945 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-200	25 U	1167 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-201	25 U	1167 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-319	25 U	1167 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-379	25 U	1167 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-439	25 U	1167 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-204	34 U	1567 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-205	34 U	1567 mm	553 mm	1000 mm	Black Grey	RAL 7021

28230-328	34 U	1567 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-388	34 U	1567 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-448	34 U	1567 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-208	38 U	1745 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-209	38 U	1745 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-332	38 U	1745 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-392	38 U	1745 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-452	38 U	1745 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-212	43 U	1967 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-213	43 U	1967 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-337	43 U	1967 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-397	43 U	1967 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-457	43 U	1967 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-216	47 U	2145 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-217	47 U	2145 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-341	47 U	2145 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-401	47 U	2145 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-461	47 U	2145 mm	553 mm	800 mm	Black Grey	RAL 7021

Table 2/2

Catalog Number	Frame Material	Product Type	Static Load	Type
----------------	----------------	--------------	-------------	------

28230-056	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-189	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-192	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-193	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-310	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-370	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-430	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-196	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-197	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-314	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-374	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-434	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-200	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-201	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-319	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-379	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-439	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-204	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-205	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty

28230-328	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-388	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-448	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-208	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-209	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-332	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-392	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-452	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-212	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-213	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-337	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-397	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-457	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-216	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-217	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-341	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-401	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty
28230-461	Aluminum	Cabinet/Rack Frame	400 kgf	Heavy Duty

ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE