


19" Telescopic Shelf for Varistar, Novastar, Eurorack, 70 kg



Varistar, Novastar and Eurorack 19" Shelf, Stationary with 70 kg load capacity, perforated for ease of assembly.

CERTIFICERINGER



FUNKTIONER

Perforated cut-outs for assembling cable ties

Static load-carrying capacity 70 kg

Incl. telescopic slides

Locking with T-bar lock possible

St, 1.5 mm

Hammer head perforation for assembly with cable ties

SPECIFIKATIONER

Product Type: Shelf

Materiale: Stål

Table 1/2

Katalognummer	Type	Bredde	Dybde	Pakke mængde	Farve	Farvekode
21130-352	Equipment Shelf	600mm	382mm	1	Black Grey	RAL 7021
21130-353	Telescopic Shelf	600mm	482mm	1	Black Grey	RAL 7021
21130-374	Telescopic Shelf	600mm	565mm	1	Black Grey	RAL 7021
21130-354	Telescopic Shelf	600mm	582mm	1	Black Grey	RAL 7021
21130-375	Telescopic Shelf	600mm	677mm	1	Black Grey	RAL 7021
21130-355	Telescopic Shelf	600mm	682mm	1	Black Grey	RAL 7021
21130-357	Telescopic Shelf	553mm	500mm	1	Black Grey	RAL 7021
21130-358	Telescopic Shelf, Reduced Depth	553mm	500mm	1	Black Grey	RAL 7021
21130-372	Telescopic Shelf	600mm	600mm	1	Black Grey	RAL 7021
21130-373	Telescopic Shelf	400mm	477mm	1	Black Grey	RAL 7021
22130-352	Telescopic Shelf	400mm	382mm	1	Light Grey	RAL 7035
22130-353	Telescopic Shelf	400mm	482mm	1	Light Grey	RAL 7035
22130-354	Telescopic Shelf	400mm	582mm	1	Light Grey	RAL 7035
22130-355	Telescopic Shelf	400mm	682mm	1	Light Grey	RAL 7035
22130-372	Telescopic Shelf	600mm	600mm	1	Light Grey	RAL 7035
22130-373	Telescopic Shelf	600mm	477mm	1	Light Grey	RAL 7035
22130-374	Telescopic Shelf	600mm	800mm	1	Black Grey	RAL 7021

Katalognummer	Type	Bredde	Dybde	Pakke mængde	Farve	Farvekode
22130-375	Telescopic Shelf	600mm	677mm	1	Light Grey	RAL 7035
27230-108	Telescopic Shelf	600mm	582mm	1	Black Grey	RAL 7021
27230-109	Telescopic Shelf	600mm	682mm	1	Black Grey	RAL 7021

Table 2/2

Katalognummer	Finish	Works With	Hurtigforsendelse
21130-352	Struktur Pulvermaling	Varistar CP	Nej
21130-353	Struktur Pulvermaling	Varistar CP	Nej
21130-374	Struktur Pulvermaling	Varistar CP	Nej
21130-354	Struktur Pulvermaling		Nej
21130-375	Struktur Pulvermaling	Varistar CP	Nej
21130-355	Struktur Pulvermaling	Varistar CP	Nej
21130-357	Struktur Pulvermaling		Nej
21130-358	Struktur Pulvermaling		Nej
21130-372	Struktur Pulvermaling	Varistar CP	Nej
21130-373	Struktur Pulvermaling	Varistar CP	Nej
22130-352	Struktur Pulvermaling		Nej
22130-353	Struktur Pulvermaling		Nej
22130-354	Struktur Pulvermaling		Nej
22130-355	Struktur Pulvermaling		Nej

Katalognummer	Finish	Works With	Hurtigforsendelse
22130-372	Struktur Pulvermaling		Nej
22130-373	Struktur Pulvermaling		Nej
22130-374	Struktur Pulvermaling		Nej
22130-375	Struktur Pulvermaling		Nej
27230-108	Struktur Pulvermaling		Nej
27230-109	Struktur Pulvermaling		Nej

YDERLIGERE PRODUKTOPLYSNINGER

Mounting bracket for assembly of telescopic slide at frame please order separately.

Please order T-bar lock separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE