

HWAT-T55 Thermostat



nVent RAYCHEM HWAT-T55 is an energy efficient thermostat for use in nVent RAYCHEM HWAT self-regulating single pipe hot water systems, in small pipe networks or for branch lines.

FEATURES

Simple to install and operate: digital display for temperature and alarm, 35 mm DIN-Rail mountable

Energy saving: 3 operating modes ON/ECO/OFF; with HWAT-L the system can be switched ON/OFF during absence periods, with HWAT-M/R there are three preset temperatures 55/50/45 °C, integrated clock and energy savings (ECO) for off-peak usage

System monitoring through high temperature alarm: if a temperature over 66 °C is measured the system will be switched off to avoid scalding and calcification

System monitoring through low temperature alarm: to avoid unnecessary energy consumption when hot water storage problems occur

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

Table 1/3

Catalog Number	Item Name	E-Number	IP Rating	Voltage Rating	Voltage Rating Type	Adjustment Range
1244-015722	HWAT-T55	9935501413	IP20	195 – 253 V	AC	40 – 60 °C

Table 2/3

Catalog Number	Item Name	E-Number	Nominal Switching Current @ 250V, Potential Free	Power Consumption, Standby	Height	Width
1244-015722	HWAT-T55	9935501413	16 A	5 W	87.5 mm	52.5 mm

Table 3/3

Catalog Number	Item Name	E-Number	Depth
1244-015722	HWAT-T55	9935501413	87.5 mm

ADDITIONAL PRODUCT DETAILS

The nVent RAYCHEM HWAT-T55 thermostat is designed for use with HWAT-L, -M or -R. Maximum circuit length is limited to 50 m. For temperature adjustment, consider local hygienic standards.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT