


AMC Filler Module With Pull-Handle



This AdvancedMC filler module consists of a stainless steel front panel without LEDs and has EMC gaskets on the left hand and bottom side. The filler module is fixed into the chassis card guide by a snap in plastic nose. The module can be used to cover an empty slot, to ensure EMC shielding and close the front to seal air leaks into the chassis. These filler modules can be used in AdvancedMC Carriers and in MicroTCA slots. It doesn't require a locking bar.

CERTIFICERINGER



FUNKTIONER

In accordance with AMC.0 R2.0 specification

Shielded filler modules are used to close unused slots

pull handle to extract sub-assembly

The optional air baffle (airflow adjustable) can be used to direct chassis airflow

SPECIFIKATIONER

Produktfamilie: AdvancedMC
Type: Filler Module
Product Type: System Module

Table 1/1

Katalognummer	Design Feature	Materiale	Finish	Pakke mængde	Hurtigforsendelse
20849-249	Mid-Size	Aluminium	Passivated	1	Nej
20849-022	Compact	Stainless Steel		1	Nej

Katalognummer	Design Feature	Materiale	Finish	Pakke mængde	Hurtigforsendelse
20849-250	Full-Size	Aluminium	Passivated	1	Nej
20849-106	Mid-Size	Stainless Steel		1	Nej
20849-248	Mid-Size	Aluminium	Passivated	1	Nej
20849-025	Full-Size	Stainless Steel		1	Nej
20849-251	Full-Size	Aluminium	Passivated	1	Nej
20849-024	Full-Size	Stainless Steel		1	Nej
20849-107	Mid-Size	Stainless Steel		1	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE